



Mirage Micro™

NASAL MASK

PROVEN SEAL, PERFECT FIT

The latest generation nasal mask from ResMed provides personalised fit, seal and comfort for over 95% of users.¹ Working with the proven Mirage™ dual-wall cushion,


the mask's unique MicroFit™ dial fine-tunes the fit to suit each individual user. Intuitive to use for sleep professionals and users, Mirage Micro is the new benchmark in nasal masks.

MicroFit dial
offers 24 positions for better fit, seal and comfort

Streamlined forehead support
provides clear field of vision due to sleek, stylish design

Quiet vent design
provides minimal noise output; removable cover for easy cleaning

360° elbow rotation
positions the tubing for maximum comfort



Elbow partition
aids CO₂ washout and reduces noise output




Mirage dual-wall cushion
reduces pressure on nasal bridge and seals effectively; tab allows easy removal of cushion from frame

Set-and-forget headgear clips
retain optimal headgear settings; easy to attach and detach

Swivel
offers a convenient way to connect and disconnect air tubing





TECHNOLOGY HIGHLIGHT

MicroFit dial

A choice of 24 positions at your fingertips—providing a comfortable, effective fit for over 95% of users¹

- **Adjustable:** can easily be adjusted while on the user's face
- **Precise:** each turn of the dial adjusts the forehead support in small increments
- **Progressive:** moves in towards the face, allowing the user to sense when the fit is most comfortable for them
- **Works in combination with the cushion:** as the dial adjusts the angle of the mask to the face, the dual-wall cushion adapts to enhance the seal without the need for overtightening the headgear

USER BENEFITS

Personalised fit and comfort

- MicroFit dial fine-tunes the fit to suit each user's profile
- Mirage dual-wall cushion is available in five sizes, including new Small size, to fit more than 95% of users¹
- Deep mask frame design accommodates a greater range of nasal structures

Quiet, sleek and stylish

- Array of small, built-in vents diffuse air quietly²
- Quiet therapy for a good night's sleep, with mask noise at a minimal 28.3dB²
- Streamlined design feels light on the face

Intuitively easy

- MicroFit dial is easily adjusted with one hand even while lying down
- Vent cover can be removed for easy and hygienic cleaning
- Intuitive mask design for easy handling, cleaning, assembly and disassembly

PROFESSIONAL BENEFITS

First-time fit for over 95% of users¹

- Combination of MicroFit dial and dual-wall cushion achieves a perfect fit for a range of facial structures—first time, every time
- Five cushion sizes including new Small size (cushion and frame) fit a wider range of users

Customer satisfaction and compliance

- Increased therapy acceptance through first-time fit
- Personalised fit, comfort and seal encourage long-term compliance
- Mask parts designed for fast and intuitive assembly and disassembly
- Comprehensive user support package including travel bag and user guide with mask fitting and care instructions

Cost and time efficiencies

- Reduced fitting and training time: dial and cushion combination seals quickly
- Reduced callbacks: ease of use and fitting
- Reduced inventory: two frame sizes fit five cushion sizes; five cushions, only three product codes



PRODUCT CODES

Mirage Micro Nasal Mask

Australia, New Zealand

Small	16363
Medium and Large	16364
Large Wide and X-Large	16365

¹ Source: internal ResMed anthropometric data

² Source: ResMed tests as per ISO 3744:1994